



HYDROTAP G5 ULTRACARE BCU40 UV NON-CARBON FILTER CLASSIC ACCESSIBLE TAP CHROME



BOILING

CHILLED

FILTERED



Order Code H5D7U1Z00AUC

Zip HydroTap UltraCare Boiling, Chilled Filtered water system features antimicrobial protection impregnated into key water paths for enhanced hygiene, LED UV-C disinfection, 0.2 micron carbon free internal filtration, Life cycle maintenance plan in a single under bench command centre including full colour interactive touch screen display with pin code protection and customisable settings including boiling water safety mode, 2 energy saving modes including ON/OFF timers and 2 hour sleep mode, 'Quiet' mode with automated intelligent fan speed adjustment, and 100% water efficient air cooled technology. Easy to install integrated ventilation tray included.

Manufacturing Code	H5D7U1Z00AUC
Capacity	Commercial
Boiling Cups per hour	160
Chilled Cups per hour	125

Tap	Zip HydroTap CLASSIC ACCESSIBLE Tap (Chrome)
Water Pressure	Min 170kPa - Max 700kPa
Water Connection	1/2" BSP (G1/2)
Water Supply Requirements	Cold
Water Valves	Integrated 500kPa Pressure limiting valve and Dual Check Valve
Power Rating	1.97kW 220-240V 50Hz
Power Supply	2 x 10 Amp socket outlet
Dimensions	W395mm x D464mm x H333mm
Product Approvals	WaterMark, RCM, ARC
Warranty	5 years (appliance warranty 36 months plus additional 24 months tank warranty)

Installation Requirements

1. Installation and connection of your Zip HydroTap must be carried out by a qualified person, observing national and local regulations.
 2. You will require suitable mains electrical and drinking water connections, plus waste water drainage all within 1 metre of the product.
 3. Zip Micro is air-cooled so discrete cabinetry cut-outs are required for ventilation.
 4. Installation on most bench tops is straightforward however some stone bench tops may require a specialised cutting service.
 5. If you live in a hard water area, we recommend installation of a Zip scale filtration kit.
 6. Installation by Zip Professional Service can be arranged with a phone call or through www.zipwater.com/book-service-visit
-

Installation Detail

DKL2 HydroTap 09/01/00 02.21

Ventilation requirements

Contact your local service provider if ventilation is not suitable

Clearance envelope

Position the Tap and the Command Centre as close together as possible.

200
333
50
50
Command Centre width

Vent tray (kit no. 93540)

520
496
40mm adjustment
40

Detail A. Air inlet grille

max. 42
326
Cut-out in cabinet floor

Detail B. Vent Tray air outlet

max. 40
450
Cut-out in cabinet floor

HydroTap Tap options

Touch-Free Wave
214

Classic
208

Classic Accessible
219

116
Dispensing distance for all taps

Font options

Raised Font with 135mm Extension

116
351
280
116
268
20

Cutting detail

116
164
122

Font with 135mm Extension

116
351
260
104
219

Cutting detail

108
60
104
219

Mixer Tap options

Classic Mixer Tap

165
188
233
270
224

Accessible Mixer Tap

165
188
233
270

Vented mixer tap installation

Only cold water supply required

35mm hole in sink/benchtap for mixer tap
WHITE marked braided hose to HydroTap Command Centre MIXER OUT
Braided hose to HydroTap Command Centre MAINS inlet
Mains water isolation valve (not supplied)
BLUE marked braided hose to HydroTap Command Centre MIXER IN

Tap Positioning

Position the Tap to dispense into the sink, allowing clearance for a cup or teapot. Alternatively, mount on a Font (available as an accessory).

335mm hole for HydroTap Tap

Classic Plus Tap
216
210

Classic Accessible Mixer Tap (vented H option)
4mm buffer pad air space

Clearance Envelope
200 min.
333
40

IEC Flex & Plug 230-240V, 10A, 50Hz power outlet
50 min.

Air inlet
Note: should not be impeded by pipework
395

Mains cold water isolation valve (not supplied)
50 min.

464

HydroTap G5

BCU40, BCU40 H UltraCare

with "Classic Plus" Tap and Classic Accessible Mixer Tap (V)

SCALE 1:5
ALL DIMENSIONS IN MM UNLESS OTHERWISE SPECIFIED. INSTALLATION DIAGRAMS ARE FOR ILLUSTRATIVE PURPOSES ONLY. HOSES ARE NOT SHOWN TO SCALE AND CANNOT BE LENGTHENED.